

Specification Sheet

Part Number: 183-05037



- Excellent fire-safety characteristics.
- Narrow slots suitable for small-diameter wires.
- Fingers can be removed with no sharp edges at pre-notched snap-off points.
- Duct covers hold securely even in a vertical position and under vibration.

Halogen Free Slotted Wiring Duct, w/o Adhesive, 50mm x 37.5mm, PC/ABS, Gray RAL, 32 m/Box

Article Number	183-05037
Type	HTWD-HF-50X37.5
Color	Gray RAL 7035 (7035)
Quantity Per	box
Product Description	HellermannTyton HTWD-HF halogen-free ducts are used wherever there are high demands on personal or material safety, such as public transport, tunnels, escalators and data processing centers. Snap-on covers are included with corresponding duct sizes to ensure complete wire protection. Base perforation according to DIN EN 50085. Note: Halogen-free PC+ABS is not resistant to all oils and greases.
Short Description	Halogen Free Slotted Wiring Duct, w/o Adhesive, 50mm x 37.5mm, PC/ABS, Gray RAL, 32 m/Box

Global Part Name	HTWD-HF-50X37.5-PC/ABS-GY
Length L (Imperial)	6.56
Length L (Metric)	2
Fixation Method	Screw Mounting
Width W (Imperial)	1.97
Width W (Metric)	50
Height H (Imperial)	1.48
Height H (Metric)	37.5
Material	Acrylonitrile Butadiene Styrene alloyed with Polycarbonate (PC/ABS)
Material Shortcut	PC/ABS
Flammability	UL 94 V-0
Halogen Free	Yes
Operating Temperature	-13°F to +194°F (-25°C to +90°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Certification/Specification	DIN EN [45545-2]
Package Quantity (Imperial)	104.9
Package Quantity (Metric)	32
Customs Number	3925900000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[183-05037](#)