

Specification Sheet

Part Number: 184-05558



Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

High-Density Slotted-Wall Wiring Duct, 3" x 5", Non-Adhesive, PVC, White, 30ft/box

| | |
|---------------------|--|
| Article Number | 184-05558 |
| Type | SLHD3X5 |
| Color | White (WH) |
| Quantity Per | box |
| Product Description | HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |
| Short Description | High-Density Slotted-Wall Wiring Duct, 3" x 5", Non-Adhesive, PVC, White, 30ft/box |

| | |
|-------------------------|----------------|
| Global Part Name | SLHD3X5-PVC-WH |
|-------------------------|----------------|

| | |
|----------------------------|-----|
| Length L (Imperial) | 6.0 |
|----------------------------|-----|

| | |
|--------------------------|------|
| Length L (Metric) | 1.83 |
|--------------------------|------|

| | |
|---------------------------|-----|
| Width W (Imperial) | 3.0 |
|---------------------------|-----|

| | |
|-------------------------|------|
| Width W (Metric) | 76.2 |
|-------------------------|------|

| | |
|----------------------------|------|
| Height H (Imperial) | 5.06 |
|----------------------------|------|

| | |
|--------------------------|-------|
| Height H (Metric) | 128.5 |
|--------------------------|-------|

| | |
|---|-----|
| Mounting Hole Centers (Imperial) | 2.0 |
|---|-----|

| | |
|-----------------|-------------------------|
| Material | Polyvinylchloride (PVC) |
|-----------------|-------------------------|

| | |
|--------------------------|-----|
| Material Shortcut | PVC |
|--------------------------|-----|

| | |
|---------------------|--------------------|
| Flammability | Self-extinguishing |
|---------------------|--------------------|

| | |
|---------------------|----|
| Halogen Free | No |
|---------------------|----|

| | |
|------------------------------|----------------|
| Operating Temperature | +122°F (+50°C) |
|------------------------------|----------------|

| | |
|-------------------------------------|----|
| Reach Compliant (Article 33) | No |
|-------------------------------------|----|

| | |
|------------------------------------|--|
| ROHS Compliant | Yes |
| Certification/Specification | EN 50085-1:2005 + A1:2013 CSA UL EN 50085-2-3_1A |
| UL Recognized (US) | Yes |
| Package Quantity (Imperial) | 30 |
| Package Quantity (Metric) | 9.14 |
| Customs Number | 3925900000 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[184-05558](#)