

Specification Sheet

Part Number: 184-12001



Narrow fingers reduce fanning of wires to terminal blocks, providing a neater appearance.

Each finger features a double restriction to hold wires in the bottom portion of the duct, simplifying installation.

Mounting holes are uniform in size to those in slotted and solid wall duct but are provided every two inches to accommodate compact designs and provide ease of installation.

Nonpermanent adhesive allows repositioning prior to final installation.

High-Density Slotted-Wall Wiring Duct, 1" x 2", Adhesive, PVC, Gray, 30ft/box

|                     |  |
|---------------------|--|
| Article Number      | 184-12001  |
| Type                | SLHDA1X2   |
| Color               | Gray (GY)  |
| Quantity Per        | box  |
| Product Description | HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated. |

|                                  |   |
|----------------------------------|---|
| Short Description                | High-Density Slotted-Wall Wiring Duct, 1" x 2", Adhesive, PVC, Gray, 30ft/box |
| Global Part Name                 | SLHDA1X2-PVC-GY   |
| Length L (Imperial)              | 6.0   |
| Length L (Metric)                | 1.83  |
| Width W (Imperial)               | 1.0   |
| Width W (Metric)                 | 25.4  |
| Height H (Imperial)              | 2.07  |
| Height H (Metric)                | 52.6  |
| Mounting Hole Centers (Imperial) | 2.0   |
| Material                         | Polyvinylchloride (PVC)   |
| Material Shortcut                | PVC   |
| Halogen Free                     | No  |
| UV Resistant (Yes/No)            | No  |
| Operating Temperature            | +122°F (+50°C)  |

|                              |  |
|------------------------------|--|
| Reach Compliant (Article 33) | No   |
| ROHS Compliant               | Yes  |
| Certification/Specification  | UL EN 50085-1:2005 + A1:2013 CSA EN 50085-2-3_1A |
| UL Recognized (US)           | Yes  |
| Package Quantity (Imperial)  | 30.0   |
| Package Quantity (Metric)    | 9.14   |
| Customs Number               | 3925900000                                       |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[184-12001](#)