

Specification Sheet

Part Number: 184-22025



Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.

High-Density Slotted-Wall Wiring Duct, 2" x 3", Non-Adhesive, PVC, Black, 30ft/box

Article Number	184-22025
Type	SLHD2X3
Color	Black (BK)
Quantity Per	box
Product Description	HellermannTyton High-Density Slotted Wall Wiring Duct features narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and components are more easily accommodated.
Short Description	High-Density Slotted-Wall Wiring Duct, 2" x 3", Non-Adhesive, PVC, Black, 30ft/box

<b>Global Part Name</b>	SLHD2X3-PVC-BK
-------------------------	----------------

<b>Length L (Imperial)</b>	6.0
----------------------------	-----

<b>Length L (Metric)</b>	1.83
--------------------------	------

<b>Width W (Imperial)</b>	2.0
---------------------------	-----

<b>Width W (Metric)</b>	50.8
-------------------------	------

<b>Height H (Imperial)</b>	3.07
----------------------------	------

<b>Height H (Metric)</b>	77.9
--------------------------	------

<b>Mounting Hole Centers (Imperial)</b>	2.0
---	-----

<b>Material</b>	Polyvinylchloride (PVC)
-----------------	-------------------------

<b>Material Shortcut</b>	PVC
--------------------------	-----

<b>Flammability</b>	Self-extinguishing
---------------------	--------------------

<b>Halogen Free</b>	No
---------------------	----

<b>Operating Temperature</b>	+122°F (+50°C)
------------------------------	----------------

<b>Reach Compliant (Article 33)</b>	No
-------------------------------------	----

<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	EN 50085-1:2005 + A1:2013 UL EN 50085-2-3_1A CSA
<b>UL Recognized (US)</b>	Yes
<b>Package Quantity (Imperial)</b>	30
<b>Package Quantity (Metric)</b>	9.14
<b>Customs Number</b>	3925900000

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[184-22025](#)