

Specification Sheet

Part Number: SNP210C2

Installation and removal can be five times faster
than conventional clamps

.

Heat stabilized material is suitable for high temperature applications.

Completely reusable

.

Will not rust or corrode

.


Safety engineered.

No protruding band or cluster.

Can be installed with hose in place

.

One-hand installation for tight places.



Snapper Hose Clamp, 0.35 - 0.40" Bundle Diameter, POM, White, 100/pkg

Article Number

190-00101

Type

SNP2

Color	White (WH)
Quantity Per	bag
Product Description	The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. These white polyacetal Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. Custom design and color options are available based upon application and volume requirements.
Short Description	Snapper Hose Clamp, 0.35 - 0.40" Bundle Diameter, POM, White, 100/pkg
Global Part Name	SNP2-POM-WH
Length L (Imperial)	0.83
Length L (Metric)	21.0
Fixation Method	Plug-in mounting
Variant	Closed
Bundle Diameter Min (Imperial)	0.334
Bundle Diameter Min (Metric)	8.7
Bundle Diameter Max (Imperial)	0.4
Bundle Diameter Max (Metric)	10.0
Wall Thickness WT (Imperial)	.067

Wall Thickness WT (Metric)	1.7
Material	Polyacetal (POM)
Material Shortcut	POM
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +194°F (-40°C to +90°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[SNP210C2](#)