

Specification Sheet

Part Number: SNP3210H4

Installation and removal can be five times faster than conventional clamps.

Heat stabilized material is suitable for high temperature applications.

Completely reusable.

Will not rust or corrode.

Safety engineered.

No protruding band or cluster.

Can be installed with hose in place.

One-hand installation for tight places.



Snapper Hose Clamp, 1.21 - 1.38" Bundle Diameter, POM, White, 500/pkg

| | |
|----------------|-----------|
| Article Number | 190-00143 |
|----------------|-----------|

| | |
|------|-------|
| Type | SNP32 |
|------|-------|

| | |
|-------|------------|
| Color | White (WH) |
|-------|------------|

| | |
|--------------|-----|
| Quantity Per | bag |
|--------------|-----|

| | |
|------------------------------|--|
| Product Description | The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. These white polyacetal Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. Custom design and color options are available based upon application and volume requirements. |
| Short Description | Snapper Hose Clamp, 1.21 - 1.38" Bundle Diameter, POM, White, 500/pkg |
| Global Part Name | SNP32-POM-WH |
| Fixation Method | Plug-in mounting |
| Variant | Closed |
| Bundle Diameter Min (Metric) | 30.9 |
| Bundle Diameter Max (Metric) | 35.7 |
| Wall Thickness WT (Imperial) | .068 |
| Wall Thickness WT (Metric) | 1.7 |
| Material | Polyacetal (POM) |
| Material Shortcut | POM |
| Flammability | UL 94 HB |

| | |
|------------------------------|----------------------------------|
| UV Resistant (Yes/No) | No |
| Operating Temperature | -40°F to +194°F (-40°C to +90°C) |
| Reach Compliant (Article 33) | No |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 500 |
| Customs Number | 3926909988 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[SNP3210H4](#)