

Specification Sheet

Part Number: SNP3810H4

- Installation and removal can be five times faster than conventional clamps.
- Heat stabilized material is suitable for high temperature applications.
- Completely reusable.
- Will not rust or corrode.
- Safety engineered.
- No protruding band or cluster.
- Can be installed with hose in place.
- One-hand installation for tight places.



Snapper Hose Clamp, 1.62 - 1.89" Bundle Diameter, POM, White, 500/pkg

Article Number 190-00245

Type SNP38

Color White (WH)

Quantity Per pack

Product Description

The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. These white polyacetal Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. Custom design and color options are available based upon application and volume requirements.

Short Description

Snapper Hose Clamp, 1.62 - 1.89" Bundle Diameter, POM, White, 500/pkg

Global Part Name

SNP38-POM-WH

Fixation Method

Plug-in mounting

Variant

Closed

Bundle Diameter Min (Imperial)

1.61

Bundle Diameter Min (Metric)

41.0

Bundle Diameter Max (Imperial)

1.89

Bundle Diameter Max (Metric)

48.1

Wall Thickness WT (Imperial)

.068

Wall Thickness WT (Metric)

1.7

Material

Polyacetal (POM)

Material Shortcut

POM

Flammability

UL 94 HB

UV Resistant (Yes/No)

No

Use Conditions

For Indoor and Outdoor Use

Operating Temperature

-40°F to +194°F (-40°C to +90°C)

Reach Compliant (Article 33)

Yes

RoHS Compliant

Yes

Package Quantity (Imperial)

500

Package Quantity (Metric)

500

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[SNP3810H4](#)