

Specification Sheet

Part Number: TSRP3I-33-1

Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.

PVC construction is lightweight, durable and more affordable than metallic raceway systems.


Flexible hinge designed to reduce stress cracking and discoloration from repeated opening and closing.

Systems and fittings are available in white, office white and ivory to coordinate with a variety of décor.

Fittings incorporate a minimum 1" bend radius to meet TIA/EIA 568-B and 569-A standards.

Enhanced "channel and lug" mating design provides a tighter, more secure fit between raceway lengths and fittings.

System is UL Listed for power up to 600 volts and meet UL5A and CSA 22.2.



Internal Corner Cover, 1-3/4", 1" Bend Radius, PVC, Ivory, 1/bg

Article Number 250-63332

Type TSRP3-33-1

Color Ivory (IV)

Quantity Per pack

Product Description

HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. TSRP surface raceway systems are designed to aesthetically organize and route either power or communications cables.

Short Description

Internal Corner Cover, 1-3/4", 1" Bend Radius, PVC, Ivory, 1/bg

Global Part Name

TSRP3-33-1-PVC-BGE

Width W (Imperial)

1.75

Material

Polyvinylchloride (PVC)

Material Shortcut

PVC

Flammability

UL 94 V-0

Halogen Free

No

UV Resistant (Yes/No)

No

Use Conditions

For Indoor Use Only

Operating Temperature

+122°F (+50°C)

| | |
|------------------------------|------------|
| Reach Compliant (Article 33) | No |
| ROHS Compliant | Yes |
| UL Listed (US and Canada) | Yes |
| UL Listed (US) | Yes |
| | |
| | |
| Package Quantity (Imperial) | 1 |
| | |
| Package Quantity (Metric) | 1 |
| | |
| Customs Number | 3925900000 |

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TSRP3I-33-1](#)