


Specification Sheet

Part Number: FPF



Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.

Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.

Grommet, Panel Thickness 0.256"-0.319", PE, Natural, 82ft/pkg

Article Number 251-10609

Type G51PF

Color Natural (NA)

Quantity Per reel

Product Description HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

Short Description Grommet, Panel Thickness 0.256"-0.319", PE, Natural, 82ft/pkg

Global Part Name G51PF-PE-NA

Length L (Imperial) 82.0

Variant Open

Width W (Imperial) 0.449

Width W (Metric) 11.4

Height H (Imperial) 0.268

Height H (Metric) 6.8

Panel Thickness Min (Imperial) 0.26

Panel Thickness Max (Imperial) 0.32

Panel Thickness Min (Metric) 6.5

Panel Thickness Max (Metric) 8.1

Material Polyethylene (PE)

Material Shortcut PE

Flammability UL 94 HB

Halogen Free Yes

UV Resistant (Yes/No) No

Operating Temperature	-22°F to +176°F (-30°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	82
Package Quantity (Metric)	25
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FPF](#)