

Specification Sheet

Part Number: 321-50010



Tubing is 3.5:1, thick wall adhesive lined.

Toughness and weatherability is ideal for low and medium voltage power applications.

Available in 3.28' (1.0 m) lengths, multiple diameters and 1 color (black).

Conveniently packed in a display carton.

Heat Shrink Tubing, 4' Long Stick, Thick Wall Adhesive Lined, Up to 3.5:1, 1/2", 13/4 dia, PO, Black, 6/pkg

Article Number

321-50010

Type

TREDUX HA47-48ST-13/4

Color

Black (BK)

Quantity Per

pcs.

Product Description

HA47 is a thick-wall adhesive lined heat shrink tubing for use in applications up to 1000 volts. The adhesive lining provides excellent moisture sealing and weather protection, making it suitable for above and below ground applications. Made of a polyolefin outer material, this tubing has a shrink ratio up to 3.5 to 1. The adhesive lining begins to activate as the temperature approaches 185° F (85° C).

Short Description

Heat Shrink Tubing, 4' Long Stick, Thick Wall Adhesive Lined, Up to 3.5:1, 1/2", 13/4 dia, PO, Black, 6/pkg

| | |
|------------------|-------------------------------|
| Global Part Name | TREDUX HA47-48ST-13/4-PO-X-BK |
|------------------|-------------------------------|

| | |
|---------------------|-----|
| Length L (Imperial) | 4.0 |
|---------------------|-----|

| | |
|-------------------|-----|
| Length L (Metric) | 1.0 |
|-------------------|-----|

| | |
|---------------|-------------|
| Voltage Range | Low Voltage |
|---------------|-------------|

| | |
|---------|------------|
| Variant | Thick-Wall |
|---------|------------|

| | |
|-----------------------------|-----|
| Nominal Diameter (Imperial) | 0.5 |
|-----------------------------|-----|

| | |
|---------------------------|----|
| Nominal Diameter (Metric) | 13 |
|---------------------------|----|

| | |
|------------------------------|------|
| Wall Thickness WT (Imperial) | .094 |
|------------------------------|------|

| | |
|----------------------------|-----|
| Wall Thickness WT (Metric) | 2.4 |
|----------------------------|-----|

| | |
|----------|---------------------------------|
| Material | Polyolefin, cross-linked (PO-X) |
|----------|---------------------------------|

| | |
|-------------------|------|
| Material Shortcut | PO-X |
|-------------------|------|

| | |
|----------|-------------------|
| Adhesive | Hot melt adhesive |
|----------|-------------------|

| | |
|--------------|-----|
| Halogen Free | Yes |
|--------------|-----|

| | |
|-----------------------|----|
| UV Resistant (Yes/No) | No |
|-----------------------|----|

| | |
|-----------------------|-----------------------------------|
| Operating Temperature | -67°F to +230°F (-55°C to +110°C) |
|-----------------------|-----------------------------------|

| | |
|------------------------------|------------|
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 6 |
| Package Quantity (Metric) | 6 |
| Customs Number | 3926909988 |
| Weight (Imperial) | 1 |

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[321-50010](#)