

Specification Sheet

Part Number: 544-80102



Raised marking ensure text visibility even when covered in dust, debris, grease and oil.
Stainless steel grade SS316 is suited for use in harsh environments.
Marker plates are designed for use with stainless steel cable ties with a 0.81" (4.6mm) strap width.

M-Boss Marker, 3.54" Wide x 0.39" High, Stainless Steel, Silver, 500/Box

Article Number	544-80102
Type	MBML10X90
Color	Metal (ML)
Quantity Per	box
Product Description	M-BOSS Compact Markers are used in all areas where severe mechanical or chemical conditions occur, such as offshore industry, solar industry, marine engineering, petrochemical industry, mining, underground or on radio and cellular masts where mark permanence is critical.
Short Description	M-Boss Marker, 3.54" Wide x 0.39" High, Stainless Steel, Silver, 500/Box

Global Part Name	MBML10X90-SS316-ML
Technical Description	M-Boss Marker, .39" Wide X 3.54" Long, Silver
Length L (Imperial)	3.54
Length L (Metric)	89.5
Fixation Method	Others
Variant	Other
Width W (Imperial)	3.54
Width W (Metric)	10
Height H (Imperial)	0.39
Height H (Metric)	9.91
Diameter D (Imperial)	0.236
Diameter D (Metric)	6
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.6
Bolt Size	MBT Metal ties max width 4.6 mm

Material	Stainless Steel (SS316)
Material Shortcut	SS316
Halogen Free	Yes
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	7326908695

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[544-80102](#)