

Specification Sheet

Part Number: 553-50063

Versatile

Flexible, flame retardant, heat shrinkable polyolefin tubing meets all military specification.

3:1 shrink ratio enables a wide range of wire sizes to be covered.

Standard colors - yellow, white and black.

Larger pack options result in less box changes.

High Performance Design

Center slit and multiple slit versions reduce or eliminate hand cutting.

Nonslip printable liner allows additional marker data to be printed on the reverse side for records and placement instructions.

Use HellermannTyton's Durattach ribbon system for the highest print performance on the market.

Reduce Printer Jams

Custom box opening allows markers to dispense directly into HellermannTyton thermal transfer printers.

Dispense markers faster and easier with waxed core dispenser.



ShrinkTrak Labels, 1-Sided, 4-Slit, 0.125" (3.17mm), PO-X, White, 1000/box

Article Number	553-50063
Type	HST3-1WH-3S
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
Short Description	ShrinkTrak Labels, 1-Sided, 4-Slit, 0.125" (3.17mm), PO-X, White, 1000/box
Global Part Name	HST3-1WH-3S-PO-X-WH
Variant	Thin-Wall
Width W (Imperial)	0.475
Width W (Metric)	12.07
Thickness T (Imperial)	.003
Thickness T (Metric)	.0762
Height H (Imperial)	0.235
Height H (Metric)	5.69

Width of Liner (Metric)	76.2
Width of Liner (Imperial)	3.0
Outside Diameter OD (Imperial)	0.125
Outside Diameter OD (Metric)	3.2
Outside Diameter Max (Imperial)	0.125
Outside Diameter Max (Metric)	3.2
Wall Thickness WT (Imperial)	0.031
Wall Thickness WT (Metric)	0.79
Material	Polyolefin, cross-linked (PO-X)
Material Shortcut	PO-X
US MIL SPEC	SAE-AMS-DTL-23053/5 Class 1 and 3 MIL-STD-202G Method 215K SAE-AS81531
Flammability	UL 224 VW-1
Halogen Free	No
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only

Operating Temperature	-67°F to +275°F (-55°C to +135°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	CEN
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3917320000
Labels per Column	1
Labels per Row	4

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-50063](#)