

Specification Sheet

Part Number: 556-26006



- Halogen free for low-smoke and low-fire hazard applications.
- White front and yellow back for versatility.
- Superior strength and tear resistance for long lasting identification.
- Pre-cut slots to secure the TipTags using HellermannTyton cable ties.

TipTag, 2.59" x .50", PO/Polyester, White/Yellow, 500/roll

Article Number	556-26006
Type	TIPTAGVA10X65YEWB
Color	Yellow (YE) White (WB)
Quantity Per	pack
Product Description	TIPTAGs are halogen free, tear resistant, and lightweight cross laminated polyolefin tags ideal for use where weight is a critical factor. Each side is a different color. One side is yellow and the other side is White so that a high contrast black on yellow or black on white mark can be printed.
Short Description	TipTag, 2.59" x .50", PO/Polyester, White/Yellow, 500/roll
Global Part Name	TIPTAGVA10X65YEWB-PO-WB/YE

Fixation Method	Others
Variant	Other
Width W (Imperial)	2.59
Width W (Metric)	65.0
Height H (Imperial)	0.5
Height H (Metric)	12.7
Material	Polyolefin (PO)
Material Shortcut	PO
US MIL SPEC	SAE-AS81531 MIL-STD-202G Method 215K
Halogen Free	Yes
Operating Temperature	-58°F to +221°F (-50°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	MIL-STD-202G Method 215K BS-4G-198-3, Type 11a SAE - AS81531

Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3921905050

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[556-26006](#)