

Specification Sheet

Part Number: 558-00358

Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options.

The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment.

Signs can be designed in TagPrint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.

Adhesive Labels, Solid Color Continuous Roll, 4.0" x 250', VL, Yellow, 250ft/roll

Article Number 558-00358

Type HT4YE250

Color Yellow (YE)

Quantity Per roll

Product Description Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.

Short Description	Adhesive Labels, Solid Color Continuous Roll, 4.0" x 250', VL, Yellow, 250ft/roll
Global Part Name	HT4YE250-V-YE
Technical Description	Solid Colored Continuous Roll, 4.0" X 250', Yellow
Length L (Imperial)	250.0
Length L (Metric)	76.20
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	4.0
Width W (Metric)	101.6
Width of Liner (Metric)	101.6
Width of Liner (Imperial)	4.0
Material	Vinyl (V)
Material Shortcut	V
Adhesive	Acrylic
Halogen Free	No

UV Resistant (Yes/No)	Yes
Adhesive Operating Temperature	-40°F to +180°F (-40°C to +82°C)
Operating Temperature	-40°F to +180°F (-40°C to +82°C)
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2011 NEC2014 NEC2017 NEC2020
UL Recognized (US)	Yes
 	
Package Quantity (Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[558-00358](#)