

Specification Sheet

Part Number: 558-00501



Continuous Polyester Labels are made with UV stable materials for long outdoor life.
Labels use UV stable permanent ink.

Continuous polyester is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

Adhesive Labels, Solid Color Continuous Roll, 1.0" x 250', UV Stable PET, Red, 250ft/roll

Article Number	558-00501
Type	HT1RDHB250
Color	Red (RD)
Quantity Per	roll
Product Description	Colored continuous rolls offer a high bond adhesive that is sustainable for low surface energy substrates such as the low density plastics on the front of an inverter or powder coat paint surfaces. The adhesive is designed to adhere to textured surfaces without peeling or falling off.
Short Description	Adhesive Labels, Solid Color Continuous Roll, 1.0" x 250', UV Stable PET, Red, 250ft/roll

Global Part Name	HT1RDHB250-840/281-RD
Technical Description	Solid Colored Continuous Roll, Reflective, 1.0" X 250', Red
Length L (Imperial)	250.0
Length L (Metric)	76.2
Variant	3.2mil, 50lb bleached kraft paper
Width W (Imperial)	1.0
Width W (Metric)	25.4
Width of Liner (Metric)	25.4
Width of Liner (Imperial)	1.0
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)

ROHS Compliant	Yes
Certification/Specification	NEC2014 ANSI Standard Z535.4 CSA 66956 NEC2011 UL 969 IFC 2012
UL Recognized (US)	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	76.20
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[558-00501](#)