

Specification Sheet

Part Number: 591-00265



The Spirit printer is portable which allows the user to design and print signs and pipe markers remotely. Almost unlimited design and printed label formats can be made because the Spirit uses a colored continuous vinyl in a variety of colors from .5" (12.7mm) to 2.0" (50.8mm) wide. The printer has a built in cutter that cuts the vinyl to length when printed. Many colored ribbon inks allow designs that incorporate a variety of vinyl and ink colors to meet any code or visibility requirements.

Spirit Printer Refill Labels, 2.0" x 20', Reflective, VL, Red, 1/pkg

Article Number	591-00265
Type	HT2RDRF30
Color	Red (RD)
Quantity Per	roll
Product Description	The Spirit printer allows the user to design and print signs and pipe markers remotely using continuous adhesive vinyl tapes that come in a variety of colors from .5" (12.7mm) to 2.0" (50.8mm) wide. The printer has a built in cutter that cuts the vinyl to length when printed. Many colored ribbon inks allow designs that incorporate a variety of vinyl and ink colors to meet any code or visibility requirements.

Short Description	Spirit Printer Refill Labels, 2.0" x 20', Reflective, VL, Red, 1/pkg
Global Part Name	HT2RDRF30-V-RD
Technical Description	Sport Printer Refill Label Roll, 2.0" X 20', Red Reflective
Length L (Imperial)	2.0
Length L (Metric)	50.8
Fixation Method	Pasting / Stick
Variant	Roller form
Width W (Imperial)	2.0
Width W (Metric)	50.8
Height H (Imperial)	2.0
Height H (Metric)	50.80
Width of Liner (Metric)	50.8
Width of Liner (Imperial)	2.0
Material	Vinyl (V)

Material Shortcut	V
Operating Temperature	-40°F to +180°F (-40°C to +82°C)
ROHS Compliant	Yes
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	3919102055

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[591-00265](#)