

Specification Sheet

Part Number: TAG24-100

Dot matrix printable self-laminating vinyl has a smooth surface, allowing for the highest resolution and print contrast using an impact printer. The material is a conformable vinyl, allowing it to wrap and stay around wires and cable.

The acrylic-based adhesive bonds to a wide variety of substrates and will remain in place long term.

Tabtag dot matrix labels are specifically made for use in dot matrix printers for fast and easy printing.

Labels come with a pin-feed margin to ensure that they can easily be loaded into any dot matrix printing system.



Dot Matrix Label, Self-Laminating, 2.0" x .50" x 1.437", 4 Across, White, 5000/pkg

| | |
|----------------|------------|
| Article Number | 595-24100 |
| Type | TAG24 |
| Color | White (WH) |
| Quantity Per | pack |

| | |
|---------------------------------------|---|
| Product Description | HellermannTyton's self-laminating labels are used for marking wires and cable. The clear tail overlaps and protects the printed information from abrasion, chemicals and solvents and resists UV exposure. When printed using using any standard dot matrix printer, clear marking and high high-contrast imaging against the wire make this the perfect choice for durable identification. |
| Short Description | Dot Matrix Label, Self-Laminating, 2.0" x .50" x 1.437", 4 Across, White, 5000/pkg |
| Global Part Name | TAG24-100-WH |
| Fixation Method | Pasting / Stick |
| Variant | Adhesive label |
| Width W (Imperial) | 2.0 |
| Width W (Metric) | 50.8 |
| Bundle Diameter Min (Imperial) | 0.15 |
| Bundle Diameter Min (Metric) | 3.80 |
| Bundle Diameter Max (Imperial) | .29 |
| Bundle Diameter Max (Metric) | 7.60 |
| Thickness T (Metric) | 75.0 |
| Width of Liner (Metric) | 228.60 |
| Width of Liner (Imperial) | 8.9 |

| | |
|--|---|
| Outside Diameter Max (Imperial) | 0.29 |
| Outside Diameter Min (Metric) | 3.8 |
| Outside Diameter Min (Imperial) | 0.14 |
| Outside Diameter Max (Metric) | 7.60 |
| Material | Type 100, Vinyl, white, self-laminating (100) |
| Material Shortcut | 100 |
| Adhesive | Acrylic |
| Halogen Free | No |
| Adhesive Operating Temperature | -51°F to +200°F (-46°C to +93°C) |
| Operating Temperature | -51°F to +200°F (-46°C to +93°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Certification/Specification | UL-Recognized |
| UL Recognized (US) | Yes |

| | |
|------------------------------------|------------|
| Package Quantity (Imperial) | 5000 |
| Package Quantity (Metric) | 5000 |
| Customs Number | 3919905060 |
| Labels per Column | 4 |
| Labels per Row | 4 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TAG24-100](#)