

Specification Sheet

Part Number: 596-00239

Made with UV-stable inks and materials for durability and weather resistance.

Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.

High abrasion and scuff resistance for high-performance labeling.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.



Solar Label, Printable, PHOTOVOLTAIC AC DISCONNECT, 3.75" x 1.0", PET, Red, 50/roll

Article Number	596-00239
Type	PVACDIS
Color	Red (RD)
Quantity Per	roll
Product Description	Designed with cross-laminated UV stable materials, these variable print solar installation labels are designed to accept printing from any standard thermal transfer printer using a resin-based ink ribbon for the best durability. Print your voltage information directly on the label and then laminate with an optional clear acrylic laminate material for added protection. These labels can be used to print disconnecting means and breaker series directly on the labels for a more professional result and a smoother inspection process.

Short Description	Solar Label, Printable, PHOTOVOLTAIC AC DISCONNECT, 3.75" x 1.0", PET, Red, 50/roll
Global Part Name	PVACDIS-840/281-RD
Technical Description	Printable Solar Label, PHOTOVOLTAIC AC DISCONNECT (Max AC Operating Current, Nominal AC Operating Voltage), 3.75" X 1.0", Red
Local Order Number 2	Cross Reference = 10 per pack: 596-00852; Printable Metal Solar Placard 5 pack: 596-00838; Engravable Metal Solar Placard 5 pack: 596-00859; Spanish version 50 per roll: 596-00818
Width W (Imperial)	3.75
Width W (Metric)	95.25
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	1.0
Height H (Metric)	25.4
Material	Type 840/281, Polyester, UV-stabilized, clear polyester laminate (840/281)
Material Shortcut	840/281
Adhesive	Acrylic

Halogen Free	Yes
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2011 NEC2014 CSA 66956 IFC 2012
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00239](#)