

Specification Sheet

Part Number: 596-00633

Preprinted Solar Labels are made with UV-stable inks and materials for durability, weather resistance and long-term outdoor use. Polyester is resistant to chemicals and solvents and will remain legible in dirty environments.



High abrasion and scuff resistance for high performance labeling. Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Pre-Printed Header Label, WARNING, 6.0" x 4.0", UV, PET, Orange, 250/roll

Article Number	596-00633
Type	4X6WARNINGUV
Color	Orange (OG)
Quantity Per	roll
Product Description	These labels come with preprinted color headers so only one color of ribbon is needed to complete the message panel. Labels can be used with TagPrint® Pro label software and HellermannTyton thermal transfer printers to reduce labor, eliminate minimum orders and allow the user to create labels on demand.
Short Description	Pre-Printed Header Label, WARNING, 6.0" x 4.0", UV, PET, Orange, 250/roll

Global Part Name	4X6WARNINGUV-PET-OG
Technical Description	Pre-Printed Header Label, WARNING, 4" X 6", UV, Orange
Width W (Imperial)	6.0
Width W (Metric)	152.4
Thickness T (Metric)	64.0
Height H (Imperial)	4.0
Height H (Metric)	101.6
Width of Liner (Metric)	106.6
Width of Liner (Imperial)	4.2
Material	Polyester (PET)
Material Shortcut	PET
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)

Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2011 NEC2020 UL 969 CSA 66956 ANSI Standard Z535.4 NEC2017 IFC 2012 NEC2014
UL Recognized (US)	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00633](#)