

Specification Sheet

Part Number: 596-00662



- Made with UV-stable inks and materials for durability and weather resistance.
- Reflective properties to meet applicable NEC code requirements for reflective identification.
- Supplied with an aggressive adhesive to ensure long life.
- Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Solar Label, WARNING ELECTRICAL SHOCK HAZARD, 4.12" x 2.0", VL, Orange, 10/pkg

Article Number	596-00662
Type	WDCCU10
Color	Orange (OG)
Quantity Per	pack

Product Description	HellermannTyton makes it easier than ever for solar installers to meet PV labeling codes. Solar Label Convenience Packs allow installers to quickly and economically purchase high quality preprinted NEC 2014 and 2017 code-compliant solar installation labels. Packaged in 10-count quantities to meet the needs of smaller scale solar installations and independent contractors, Solar Label Convenience Packs are available in HellermannTyton's most popular preprinted NEC 2014 and 2017 code-compliant solar label formats. Each Solar Label Convenience Pack contains 10 solar installation labels. Choose from a variety of regular and reflective preprinted labels. For enhanced durability, clear laminate overlay labels are also available in a convenience pack.
Short Description	Solar Label, WARNING ELECTRICAL SHOCK HAZARD, 4.12" x 2.0", VL, Orange, 10/pkg
Global Part Name	WDCCU10-443/281-OG
Technical Description	Solar Label, Warning - DC Conductors Energized Label, 4.12" X 2.0", Orange/White
Local Order Number 2	Cross Reference = 50 per roll: 596-00588; Metal Solar Placard 5 pack: 596-00831
Width W (Imperial)	4.12
Width W (Metric)	104.6
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	2.0
Height H (Metric)	50.80

Material	Type 443/281, UV-stabilized flexible white vinyl with clear polyester laminate (443/281)
Material Shortcut	443/281
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2014
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3919905060

Labels per Column	1
-------------------	---

Labels per Row	1
----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00662](#)