

Specification Sheet

Part Number: 596-00839

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.

Aggressive adhesive ensures strong bond, even on powder coated surfaces.

Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.

Optional Paint Shields provide additional protection for pre-printed and variable data placards.

Product Image

Metal Solar Placard, Hand Writable, DC Module, 4.0" x 2.0", AA, Black, 5/pkg

Article Number

596-00839

Type

DC2011M5

Color

Black (BK)

Quantity Per

pack

Product Description

Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, hand-writable placards are designed to meet industry codes. Hand-writable placards feature a silver variable data area that can be marked using an industrial paint pen.

Short Description

Metal Solar Placard, Hand Writable, DC Module, 4.0" x 2.0", AA, Black, 5/pkg

Global Part Name	DC2011M5-AA-BK
Technical Description	4" X 2" Silver Aluminum text on black background that reads as: "RATED MAX POWER-POINT CURRENT;RATED MAX POWER-POINT CURRENT;MAXIMUM SYSTEM VOLTAGE;MAXIMUM CIRCUIT CURRENT;MAX RATED OUTPUT CURRENT OF THE CHARGE CONTROLLER (IF INSTALLED." 5 per pack. Nameplate is also printable using a paint pen to add the variable voltage information on demand.
Local Order Number 2	Cross Reference = Paint Shield: 596-00794
Length L (Imperial)	2.0
Length L (Metric)	50.8
Width W (Imperial)	4.0
Width W (Metric)	101.6
Height H (Imperial)	2.0
Height H (Metric)	50.80
Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive

Halogen Free	No
Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014
Warranty (US)	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	7616995195
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00839](#)