


Specification Sheet

Part Number: 596-00922

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.
Aggressive adhesive ensures strong bond, even on powder coated surfaces.
Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.



Optional Paint Shields provide additional protection for pre-printed and variable data placards.

Metal Solar Placard, Engravable, DC Module, 3.75" x 1.75", AA, Black, 5/pkg

Article Number	596-00922
Type	DC2017M5ENG
Color	Black (BK)
Quantity Per	pack
Product Description	Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, engravable placards are designed to meet industry codes. Engravable placards have a black area that can be engraved using standard engraving equipment.

Short Description	Metal Solar Placard, Engravable, DC Module, 3.75" x 1.75", AA, Black, 5/pkg
Global Part Name	DC2017M5ENG-AA-BK
Technical Description	3.75" X 1.75" Black text on silver aluminum background that reads as: "MAXIMUM VOLTAGE; MAXIMUM CIRCUIT CURRENT; MAX RATED OUTPUT CURRENT OF THE CHARGE CONTROLLER OR DC-TO-DC CONVERTER (IF INSTALLED)." 5 per pack. Nameplate is also printable using a paint pen to add the variable voltage information on demand.
Length L (Imperial)	1.75
Length L (Metric)	44.45
Width W (Imperial)	3.75
Width W (Metric)	95.25
Thickness T (Metric)	64.0
Height H (Imperial)	1.75
Height H (Metric)	44.45
Material	Anodized Aluminum (AA)
Material Shortcut	AA

Adhesive	Ultra High Bond Permanent Acrylic Adhesive
Halogen Free	No
Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2017
Warranty (US)	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00922](#)