

Specification Sheet

Part Number: 596-00953

HellermannTyton Voltage Markers are available in three sizes to best suit application requirements.

Glare-free surface for easy identification from any angle.

Resists moisture for long-lasting durability.

Markers are flexible to wrap securely around various size wires, pipes and conduit.



Voltage Marker, .50" x 2.25", 600 Volts, Vinyl, Orange, 17/card, 50 cards/pkg

Article Number	596-00953
Type	VM600C
Color	Orange (OG)
Quantity Per	pack
Product Description	HellermannTyton Pre-Printed Voltage Markers are made of durable vinyl and are available with the most commonly used warnings and alerts. The self-adhesive markers allow users to clearly identify electrical lines, voltages and hazards. The durable adhesive backing is resistant to UV exposure as well as chemicals and solvents. Use voltage markers on conduit, pipe, circuit boxes or electrical panels.
Short Description	Voltage Marker, .50" x 2.25", 600 Volts, Vinyl, Orange, 17/card, 50 cards/pkg

Global Part Name	VM600C-V-OG
Technical Description	Voltage Marker, 600 Volts, .50" x 2.25", 18 Per Card, 50/pkg
Length L (Imperial)	2.25
Length L (Metric)	57.15
Width W (Imperial)	2.25
Width W (Metric)	57.15
Thickness T (Imperial)	4
Thickness T (Metric)	.10
Height H (Imperial)	0.50
Height H (Metric)	12.70
Material	Vinyl (V)
Material Shortcut	V
Adhesive	Acrylic
Adhesive Operating Temperature	-40°F to +176°F (-40°C to +80°C)

Operating Temperature	-40°F to +176°F (-40°C to +80°C)
------------------------------	----------------------------------

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	50
------------------------------------	----

Package Quantity (Metric)	50
----------------------------------	----

Customs Number	3919905060
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00953](#)