

Specification Sheet

Part Number: 596-96255



Paint Mask Labels provide permanent paint protection but can still be removed at any time when required.

Paint Mask Labels withstand chemicals and heat to survive the painting process.

Paint Mask Label, 1.0" x 0.75" x 4.75", 1 Across, Polyester, White, 1000/roll

Article Number	596-96255
-----------------------	-----------

Type	PW.25W1P
-------------	----------

Color	White (WH)
--------------	------------

Quantity Per	roll
---------------------	------

Product Description	HellermannTyton thermal transfer self-laminating Paint Mask Labels are conformable with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels utilize an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.
----------------------------	--

Short Description	Paint Mask Label, 1.0" x 0.75" x 4.75", 1 Across, Polyester, White, 1000/roll
--------------------------	---

Global Part Name	PW.25W1P-PET-WH
Technical Description	Paint Mask Label, 1.0" X .75" X 4.75", 1 across,1 piece design, .25" cable diameter, Polyester, White, 1000/RL
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bundle Diameter Min (Imperial)	.125
Bundle Diameter Min (Metric)	3.17
Bundle Diameter Max (Imperial)	.375
Bundle Diameter Max (Metric)	9.52
Thickness T (Metric)	64.0
Height H (Imperial)	0.75
Height H (Metric)	19.0
Width of Liner (Metric)	50.8
Width of Liner (Imperial)	2.0
Material	Polyester Film (PET)

Material Shortcut	PET
Adhesive	Acrylic
US MIL SPEC	MIL-STD-202 MIL-STD-810G
Halogen Free	No
Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-96255](#)