

Specification Sheet

Part Number: WC1503X2

Clear laminating plastic flap permanently protects the writing and data marked on the tag.

Mounting holes for easy mounting using standard cable ties.

Markers can be mounted in any direction, either vertically, horizontally, as a wrap-around identification plate or as a flag for the best visual position on the cable assembly.



Custom Fiber Optic Tag, 4x1", PVC, 25/pkg

Article Number	597-00034
Type	WC1503
Color	Silver (SR)
Quantity Per	pack
Product Description	Custom fiber optic tag features a plastic flap to protect tag message.
Short Description	Custom Fiber Optic Tag, 4x1", PVC, 25/pkg
Global Part Name	WC1503-PVC-SR

Width W (Imperial)	4.0
Width W (Metric)	101.6
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25

Customs Number	3926909988
-----------------------	------------

Labels per Column	1
--------------------------	---

Labels per Row	1
-----------------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[WC1503X2](#)