

Specification Sheet

Part Number: GSTJC6U-GY

The slim-line design of the jack allows for a maximum of 24 modules to be fitted into a standard 19" panel

Single termination design provides consistent, repeatable terminations

The wiring manifold incorporates both TIA 568A and B wiring schemes as well as strain relief for the cable

Exceeds Category 6 performance standards, providing the highest quality standards

Suitable for air handling spaces, ideal for installation of WAPs and IP devices



GST Category 6 UTP Modular Keystone Jack, Plenum Rated, Gray, 1/bag

Article Number	852-25120
-----------------------	-----------

Type	GSTJC6U-GY
-------------	------------

Color	Gray (GY)
--------------	-----------

Quantity Per	bag
---------------------	-----

Product Description	The GST keystone jack provides a common termination method to exceed Category 6 performance standards. The slim-line design's reduced depth means there is more space at the rear of the module which allows for the higher bend radius required for large diameter cables and that they can be used in shallow trunking applications.
----------------------------	--

Short Description	GST Category 6 UTP Modular Keystone Jack, Plenum Rated, Gray, 1/bag
Global Part Name	GSTJC6U-GY
Technical Description	The design of the GST Keystone Jack has an integrated wire manifold and lid which provides integral strain relief for the cable and which enables the use of the GST Termination Tool for quick and easy installation on site.
Length L (Imperial)	0.91
Length L (Metric)	16.5
Width W (Imperial)	0.65
Width W (Metric)	16.5
Height H (Imperial)	0.63
Height H (Metric)	23.3
Depth D (Imperial)	1.54
Depth D (Metric)	38.0
UL Listed (US and Canada)	Yes
UL Listed (US)	Yes

Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8536695050
Weight (Metric)	0.006

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[GSTJC6U-GY](#)