

Specification Sheet

Part Number: PP24MOD6ASRS

- Shielded 24 ports
- Flat 1U presentation
- Integral rear management bar
- Dual labelling fields
- Accepts HT Connectivity shielded keystone jacks
- Supplied with Rack Snaps, earth cable & cable ties



Category 6A 24 Port Shielded Patch Panel With Rack-Snaps, 1U, 1/box

Article Number	853-55000
Type	PP24G6A-PA1URS-FD.XX
Color	Black (BK)
Product Description	HellermannTyton's Category 6A shielded patch panels accept HellermannTyton Shielded Category 6A jacks (RJ45FC6AS) to complete a shielded system solution. The panel provides a choice of ground stud positions on the integral grounding bar and includes rear cable management. Panels are offered in two styles, a fixed version or a sliding version to ease installation.
Short Description	Category 6A 24 Port Shielded Patch Panel With Rack-Snaps, 1U, 1/box

Global Part Name	PP24G6A-PA1URS-FD.XX
Technical Description	Category 6A 24 Port Shielded Patch Panel With Rack-Snaps, 1U
Port Count	24
Width W (Imperial)	19.0
Width W (Metric)	483.0
Height H (Imperial)	1.7
Height H (Metric)	44.0
Depth D (Imperial)	3.35
Depth D (Metric)	85.0
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	9030400000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[PP24MOD6ASRS](#)