

Specification Sheet

Part Number: PP24SMOD6AS



Integral earthing plate grounds each keystone jack helping to guarantee 10G performance by giving continuity of the 360° shielding
Rear cable management incorporated in the panel

Category 6A 1U 24 Port Sliding Shielded Patch Panel, 1/box

Article Number	853-55003
-----------------------	-----------

Type	PP24SMOD6ASRS
-------------	---------------

Product Description	HellermannTyton's Category 6A shielded patch panels accept HellermannTyton Shielded Category 6A jacks* (RJ45FC6AS) to complete a shielded system solution. The panel provides a choice of ground stud positions on the integral grounding bar and includes rear cable management. Panels are offered in two styles, a fixed version or a sliding version to ease installation. *Jacks are ordered separately
----------------------------	--

Short Description	Category 6A 1U 24 Port Sliding Shielded Patch Panel, 1/box
--------------------------	--

Global Part Name	PP24SMOD6ASRS
-------------------------	---------------

Technical Description	Category 6A - 1U 24 Port Sliding Shielded Patch Panel
------------------------------	---

Height H (Imperial)	1.7
----------------------------	-----

Height H (Metric)	44.0
--------------------------	------

Package Quantity (Imperial)	1
------------------------------------	---

Package Quantity (Metric)	1
----------------------------------	---

Customs Number	9030400000
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[PP24SMOD6AS](#)