

Specification Sheet

Part Number: PFCSC10G

Factory-polished zirconia ceramic ferrules for quick and reliable field installations.

Unique wedge clip retains connector shape for precision connection.

Easy to use- no epoxy, heat curing, polishing or special tools required.

Color coded for easy identification.

Meet ANSI/TIA/EIA 568-C standards.

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.



Connector, Fiber Optic SC Multimode OM3 (50/125), Pre-Polished (Cleave & Insert), 1/Pkg

Article Number	855-14217
-----------------------	-----------

Type	PFCSC
-------------	-------

Color	Aqua (AE)
--------------	-----------

Quantity Per	bag
---------------------	-----

Product Description	Pre-polished connectors provide high performance and eliminate the need for the time consuming task of hand polishing ferrules in the field. A factory pre-cleaved fiber stub and index-matching gel combine to offer an immediate low loss termination of single mode or multimode fiber.
----------------------------	--

Short Description	Connector, Fiber Optic SC Multimode OM3 (50/125), Pre-Polished (Cleave & Insert), 1/Pkg
Global Part Name	PFCSC
Technical Description	Pre-Polished SC 10G 50/125 Multimode Fiber Connector, Aqua
Port Count	2
Width W (Metric)	28
Height H (Metric)	9.3
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8536700000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[PFCSC10G](#)