

Specification Sheet

Part Number: CL-R20-10



Rapid installation requiring no specialized tools saves time and money. Highly repeatable – the quality of the seal is not dependent on the skill of the engineer.

Tested beyond a 20-foot water head (58.8kPa), exhibiting excellent sealing properties.

Cablelok R20 3.0 - 3.8 mm x 10, CR, Black, 1/pkg

Article Number	857-50166
-----------------------	-----------

Type	CABLELOK-R20-10
-------------	-----------------

Color	Black (BK)
--------------	------------

Quantity Per	bag
---------------------	-----

Product Description	HellermannTyton's patented Cablelok mechanical seal enables fast, safe cable installation, providing a repeatable and consistent seal between the cable and the closure port with excellent non-leak performance. Installation times are typically reduced by up to 90 percent.
----------------------------	---

Short Description	Cablelok R20 3.0 - 3.8 mm x 10, CR, Black, 1/pkg
--------------------------	--

Global Part Name	CABLELOK-R20-10
-------------------------	-----------------

Technical Description	The R Port Cablelok is a mechanical seal manufactured from external grade flexible polychloroprene. There are 11 Cablelok's which cover a cable range of 1.7mm – 9.5mm including three multi-hole versions to allow two cable drops from the same port and a port plug for blocking unused R sized drop ports.
Contents of pkg/kit	10 x CABLELOK-R20(R9), 10 x Lubricating Wipes
Port Count	1
Variant	Round - R
Material	Chloroprene Rubber (CR)
Material Shortcut	CR
Reach Compliant (Article 33)	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	9030400000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CL-R20-10](#)