

Specification Sheet

Part Number: 904-00358



Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.

Convoluted Tubing, Slit, 0.75" Dia, PEUV, Black with Orange Stripe, 4200ft/carton

Article Number	904-00358
Type	CTPUV340
Color	Black with Orange Stripe (BKSTOG)
Quantity Per	carton

<b>Product Description</b>	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.
<b>Short Description</b>	Convoluted Tubing, Slit, 0.75" Dia, PEUV, Black with Orange Stripe, 4200ft/carton
<b>Global Part Name</b>	CTPUV340-PEUV-BK
<b>Length L (Imperial)</b>	4200.0
<b>Length L (Metric)</b>	1280.2
<b>Variant</b>	Slit
<b>Inner Diameter D (Imperial)</b>	0.759
<b>Inner Diameter D (Metric)</b>	19.28
<b>Diameter D (Imperial)</b>	0.989
<b>Diameter D (Metric)</b>	25.12
<b>Outside Diameter OD (Imperial)</b>	0.989
<b>Outside Diameter OD (Metric)</b>	25.12
<b>Nominal Diameter (Imperial)</b>	0.75

<b>Nominal Diameter (Metric)</b>	19.05
<b>Wall Thickness WT (Imperial)</b>	0.005
<b>Wall Thickness WT (Metric)</b>	0.127
<b>Material</b>	Polyethylene, UV-resistant (PEUV)
<b>Material Shortcut</b>	PEUV
<b>Flammability</b>	Not flame retardant
<b>Halogen Free</b>	Yes
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>Reach Compliant (Article 33)</b>	Yes
<b>ROHS Compliant</b>	Yes
<b>Package Quantity (Imperial)</b>	4200
<b>Package Quantity (Metric)</b>	1280.20
<b>Customs Number</b>	3926909988



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[904-00358](#)