

Specification Sheet

Part Number: FERM2U



- Removable front and rear covers provide easy access to cables.
- Slide-out tray with easy-to-grip raised edge.
- Cable management spools for effective slack management.
- Optional splice trays to assist with cable splicing.
- Panel positioning for easier patch cords access.
- Round edge plastic fiber saddles for easier patch-cord routing.
- Meet ANSI/TIA/EIA 568-C standards.

Rack Mount Fiber Enclosure-Unloaded, Accepts 6 LGX Adapter Panels, 2U, Black, 1/pkg

Article Number	904-00687
Type	FERM2U
Color	Black (BK)
Quantity Per	box
Product Description	HellermannTyton rack mount enclosures are durable and support up to 1728 fibers. Rack enclosures work with standard 19" and 23" equipment racks and are designed to work with standard LGX adapter panels. HellermannTyton offers standard and GSA compliant rack mount enclosures. GSA compliant enclosures meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government projects.

Short Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 6 LGX Adapter Panels, 2U, Black, 1/pkg
Global Part Name	FERM2U-MET-BK
Technical Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 6 Adapter Panels, 2U, BK
Port Count	36 144 72
Length L (Imperial)	14.0
Length L (Metric)	355.6
Variant	Rack mount
Width W (Imperial)	17.0
Width W (Metric)	431.8
Height H (Imperial)	3.50
Height H (Metric)	88.90
Material	Metal (MET)
Material Shortcut	MET

Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8538907080

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FERM2U](#)