

Specification Sheet

Part Number: FEWM12



- Durable stainless steel construction for long life.
- Cable management spools for effective slack management.
- Bend radius control to minimize hand and wrist strain.
- Smooth grommet entry to protect cables from damage.
- Locking tab for added security.
- Meet ANSI/TIA/EIA 568-C standards.

Wall Mount Fiber Enclosure, Unloaded, accepts 2 Adapter Panels, 1 Splice Tray, Black, 1/pkg

Article Number	904-00718
Type	FEWM12
Color	Black (BK)
Quantity Per	box
Product Description	To effectively manage optical fiber terminations and splices, HellermannTyton offers a line of wall mount enclosures. They provide a termination solution for LAN applications requiring fully enclosed wall mount enclosures. This product is designed to support up to two modular adapter panels, providing the flexibility to have 12 or 16 fibers when fully loaded. This enclosure houses one splice tray.

Short Description	Wall Mount Fiber Enclosure, Unloaded, accepts 2 Adapter Panels, 1 Splice Tray, Black, 1/pkg
Global Part Name	FEWM12-MET-BK
Technical Description	Wall Mount Fiber Enclosure - Unloaded, accepts 2 Adapter Panels, 1 Splice Tray, Black
Length L (Imperial)	2.1
Length L (Metric)	53.3
Variant	Wall mount
Width W (Imperial)	13.0
Width W (Metric)	330.2
Height H (Imperial)	15.63
Height H (Metric)	397.0
Depth D (Imperial)	3.7
Depth D (Metric)	93.98
Material	Metal (MET)
Material Shortcut	MET

Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8538907080

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FEWM12](#)