

Specification Sheet

Part Number: SCSMAININSERT-I

All single mode, single mode angled and multimode 10 Gb inserts feature durable zirconia ceramic ferrules, which allow for frequent, repeated insertion.

All standard multimode inserts feature phosphor bronze ferrules, which provide an affordable insert option.

Color coded for easy fiber selection.

Meet ANSI/TIA/EIA 568-C standards.

Product Image

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.

SC Singlemode Fiber Insert, Green, Ivory, 1/pkg

Article Number

904-00747

Type

SCSMAININSERT-I

Color

Green (GN) Ivory (IV)

Quantity Per

box

Product Description

Fiber inserts provide the final connection when using fiber as a digital loop carrier, or fiber-to-the-x solution. HellermannTyton offers a variety of fiber inserts with industry standard LC, SC, ST and MTRJ connections that can be used with HellermannTyton standard flush wall plates.

Short Description

SC Singlemode Fiber Insert, Green, Ivory, 1/pkg

Global Part Name

SCSMAININSERT-I-PL-BGE/GN

Technical Description	SC Single mode Fiber Insert, Green, Ivory
------------------------------	---

Material	Plastic (PL)
-----------------	--------------

Material Shortcut	PL
--------------------------	----

Package Quantity (Imperial)	1
------------------------------------	---

Package Quantity (Metric)	1
----------------------------------	---

Customs Number	8536700000
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[SCSMAINERT-I](#)