

Specification Sheet

Part Number: LCMMINSERT-I

All single mode, single mode angled and multimode 10 Gb inserts feature durable zirconia ceramic ferrules, which allow for frequent, repeated insertion.

All standard multimode inserts feature phosphor bronze ferrules, which provide an affordable insert option.

Color coded for easy fiber selection.

Meet ANSI/TIA/EIA 568-B standards.

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.



LC Multimode Fiber Module, Beige, Ivory, 1/pkg

Article Number	904-00758
-----------------------	-----------

Type	LCMMINSERT-I
-------------	--------------

Color	Beige (BGE) Ivory (IV)
--------------	------------------------

Quantity Per	box
---------------------	-----

Product Description	Fiber inserts provide the final connection when using fiber as a digital loop carrier, or fiber-to-the-x solution. HellermannTyton offers a variety of fiber inserts with industry standard LC, SC, ST and MTRJ connections that can be used with HellermannTyton standard flush wall plates.
----------------------------	---

Short Description	LC Multimode Fiber Module, Beige, Ivory, 1/pkg
Global Part Name	LCMMINSERT-I-PL-BGE
Technical Description	LC Multimode Fiber Module, Beige, Ivory
Material	Plastic (PL)
Material Shortcut	PL
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8536700000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[LCMMINSERT-I](#)