

Specification Sheet

Part Number: FERM3U

Removable front and rear covers provide easy access to cables

Slide-out tray with easy-to-grip raised edge

Cable management spools for effective slack management

Optional splice trays to assist with cable splicing

Panel positioning for easier patch cords access

Round edge plastic fiber saddles for easier patch-cord routing

Product Image

Meet ANSI/TIA/EIA 568-C standards

Rack Mount Fiber Enclosure-Unloaded, Accepts 6 LGX Adapter Panels, 3U, BK, 1/pkg

Article Number

904-00767

Type

FERM3U

Color

Black (BK)

Quantity Per

box

Product Description

HellermannTyton wall mount and rack mount fiber enclosures provide durable protection for direct termination and splice LAN applications. Capable of supporting up to 2,304 fibers, our enclosures are equipped with cable management and routing accessories to control cable slack, limit bend radius and add strain relief control. Additional cable management spools, splice trays and splice sleeves are available for added convenience and versatility. HellermannTyton offers wall mount and rack mount fiber enclosures that work in a standard LGX footprint

Short Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 6 LGX Adapter Panels, 3U, BK, 1/pkg
Global Part Name	FERM3U-MET-BK
Technical Description	Rack Mount Fiber Enclosure-Unloaded, Accepts 6 Adapter Panels, 2U, BK
Port Count	216 54 108
Length L (Imperial)	14.0
Length L (Metric)	355.6
Variant	Rack mount
Width W (Imperial)	17.0
Width W (Metric)	431.8
Height H (Imperial)	5.25
Height H (Metric)	133.3
Material	Metal (MET)
Material Shortcut	MET

Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8538907080

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FERM3U](#)