

Specification Sheet

Part Number: RNGFAP12DMMQLC



- Ideal for installations with limited access or restricted space.
- Available in in 6 or 12 hole configuration.
- Allows ruggedized fan-outs to be presented in RapidNet Panels.
- Fits into a standard RapidNet Panel.
- Supports a maximum of 1152 fibers in 1U of space.

RapidNet Fiber Adapter Panel 12 DUP, MM, LC Aqua 1/pkg

Article Number	904-00771
Type	RNGFAP
Color	Aqua (AE)
Product Description	The RapidNet Fiber Adapter Panel is designed to allow the RapidNet solution to be used in areas with limited access or restricted space, where a RapidNet Cassette cannot be used. Panels are pre-loaded with adapters, which allow ruggedized fan-outs to be presented in RapidNet panels - offering a maximum of 288 fibers in a single adapter, or 1152 fibers in 1U of space.
Short Description	RapidNet Fiber Adapter Panel 12 DUP, MM, LC Aqua 1/pkg
Global Part Name	RNGFAP-PL-BU

Technical Description

RapidNet Fiber Adapter Panel 12 DUP, MM, LC Aqua

Port Count

24

Length L (Imperial)

2.1

Length L (Metric)

53.75

Variant

Modular Fiber Adapter Plate

Width W (Imperial)

4.0

Width W (Metric)

102.7

Height H (Imperial)

1.10

Height H (Metric)

27.80

Material

Plastic (PL)

Material Shortcut

PL

Package Quantity (Imperial)

1

Package Quantity (Metric)

1

Customs Number	8536700000
-----------------------	------------

Weight (Metric)	113.4
------------------------	-------

Weight (Imperial)	4
--------------------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[RNGFAP12DMMQLC](#)