

Specification Sheet

Part Number: VFA15SCSCOM2

Pre-radiused zirconia ceramic ferrules for precision alignment.
Industry standard LC, SC, ST or MTRJ connectors to suit specific applications.

Available in 1-5 meter lengths.


3mm cordage.

Color coded for easy identification.

Individually quality tested for insertion and return loss.

Meet ANSI/TIA/EIA 568-B standards.

Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.



FT SC - SC Duplex OM2 Fiber Assembly, 15M, Orange, 1/pkg

Article Number	904-00819
Type	VFA15SCSCOM2
Color	Orange (OG)
Quantity Per	box

Product Description	For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types – standard and GSA compliant. Our standard jumpers combine quality with value, meeting all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, GSA compliant jumpers meet Trade Agreement Act (TAA) requirements, making them acceptable for use in US government contract projects.
Short Description	FT SC - SC Duplex OM2 Fiber Assembly, 15M, Orange, 1/pkg
Global Part Name	VFA15SCSCOM2-GF-OG
Technical Description	FT SC - SC Duplex OM2 Fiber Assembly, 15M, Orange
Length L (Imperial)	49.2
Length L (Metric)	15.0
Material	Glass Fiber (GF)
Material Shortcut	GF
Package Quantity (Imperial)	1
Package Quantity (Metric)	1
Customs Number	8544700000

Weight (Metric)	340.2
------------------------	-------

Weight (Imperial)	12.0
--------------------------	------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[VFA15SCSCOM2](#)