

Specification Sheet

Part Number: VFA15LCSCOM2

- Pre-radiused zirconia ceramic ferrules for precision alignment.
- Industry standard ST, SC, MTRJ or LC connectors to suit specific applications.
- Available in 1-5 meter lengths for a variety of applications.
- Color coded for easy identification.
- Individually quality tested for insertion and return loss.
- Meet ANSI/TIA/EIA 568-B standards.
- Meet ANSI/TIA/EIA 604 (FOCIS) connector interface requirements.

Product Image

FT LC - SC Duplex OM2 Fiber Assembly, 15M, Orange, 1/pkg

Article Number	904-00823
Type	VFA15LCSCOM2
Color	Orange (OG)
Quantity Per	box

Product Description	For fiber patching requirements, HellermannTyton offers fiber optic jumpers in various lengths with a wide variety of connector configurations. HellermannTyton offers fiber jumpers in two types – standard and high performance. Our standard jumpers combine quality with value. They meet all ANSI/TIA/EIA fiber optic cable requirements while allowing installers to maximize project budgets. In addition to meeting industry standards, HellermannTyton high performance jumpers have additional features designed for high performance applications . Our high performance jumpers meet Trade Agreement Act (TAA) requirements, making them suitable for use in General Services Administration (GSA) government contract projects.
Short Description	FT LC - SC Duplex OM2 Fiber Assembly, 15M, Orange, 1/pkg
Global Part Name	VFA15LCSCOM2-GF-OG
Technical Description	FT LC - SC Duplex OM2 Fiber Assembly, 15M, Orange
Length L (Imperial)	49.2
Length L (Metric)	15.0
Material	Glass Fiber (GF)
Material Shortcut	GF
Package Quantity (Imperial)	1
Package Quantity (Metric)	1

Customs Number	8544700000
-----------------------	------------

Weight (Metric)	340.2
------------------------	-------

Weight (Imperial)	12.0
--------------------------	------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[VFA15LCSCOM2](#)