

Specification Sheet

Part Number: 904-00933



Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.

Article Number	904-00933
Type	CTPUV1140
Color	Black with Orange Stripe (BKSTOG)
Quantity Per	carton

Product Description	HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The PEUV material provides additional protection against UV radiation for long-term outdoor use.
Short Description	Convoluted Tubing, Slit, 1.25" Dia, PEUV, Black with Orange Stripe, 1800ft/carton
Global Part Name	CTPUV1140-PEUV-BK
Length L (Imperial)	1800.0
Length L (Metric)	548.64
Variant	Slit
Inner Diameter D (Imperial)	1.257
Inner Diameter D (Metric)	31.93
Diameter D (Imperial)	1.50
Diameter D (Metric)	38.10
Outside Diameter OD (Imperial)	1.50
Outside Diameter OD (Metric)	38.10

Nominal Diameter (Imperial)	1.25
Nominal Diameter (Metric)	31.75
Wall Thickness WT (Imperial)	0.006
Wall Thickness WT (Metric)	0.152
Material	Polyethylene, UV-resistant (PEUV)
Material Shortcut	PEUV
Flammability	Not flame retardant
Halogen Free	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1800
Package Quantity (Metric)	548.64
Customs Number	3926909988

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[904-00933](#)