

Specification Sheet

Part Number: CCP-SAA



Fully water sealed, achieving an IP-68 (NEMA 6P) rating, for use in wall or handhole installations.  
Separate inbound/outbound access points ensure cable sealing and segregation.  
Single subscriber splice or patch to connect a home or outdoor device.

Customer Connection Point, with SC-APC Simplex Adapter, PC, Black, 1/pkg

|                     |  |
|---------------------|--|
| Article Number      | 904-01123  |
| Type                | CCP-SAA  |
| Color               | Black (BK)   |
| Quantity Per        | EA   |
| Product Description | <p>The Customer Connection Point (CCP) is manufactured from UL 94 V-0 and UV stable black polycarbonate and has a fully detachable snap-on lid. The closure has 2 separate cable access points which are sealed with a silicon cable entry kit (cable diameter range 4.6 mm - 5.6 mm) to maintain the IP68 rating. A GORE-TEX breather membrane is fitted to the lid to prevent condensation forming in the base of the closure. The unit can be supplied with one SC Simplex or LC Duplex and matching pigtails and provides splice management for two heat shrink splices. Internal fiber management features ensure that a 30 mm minimum bend radius is maintained within the closure and provides fiber storage capacity for any excess fiber.</p> |

|                            |   |
|----------------------------|---|
| <b>Short Description</b>   | Customer Connection Point, with SC-APC Simplex Adapter, PC, Black, 1/pkg  |
| <b>Global Part Name</b>    | CCP-SAA-PC-BK   |
| <b>Contents of pkg/kit</b> | CCP Enclosure (Black), 2x Cable Entry Lock Nut, 2x Cable Entry Seal and Seal Plug (4.6–5.6 mm), CableLok Lubricating Cloth, Fiber Routing Adhesive Disk, 2x Strength Member Fixing Screws, 1x SC/APC Adapter, Installation Instructions |
| <b>Port Count</b>          | 2   |
| <b>Variant</b>             | Outdoor Enclosure   |
| <b>Width W (Imperial)</b>  | 3.5   |
| <b>Width W (Metric)</b>    | 89.0  |
| <b>Height H (Imperial)</b> | 6.30  |
| <b>Height H (Metric)</b>   | 160.0   |
| <b>Depth D (Imperial)</b>  | 1.10  |
| <b>Depth D (Metric)</b>    | 28.0  |
| <b>Material</b>            | Polycarbonate (PC)  |
| <b>Material Shortcut</b>   | PC  |

|                                    |            |
|------------------------------------|------------|
| <b>Package Quantity (Imperial)</b> | 1          |
| <b>Package Quantity (Metric)</b>   | 1          |
| <b>Customs Number</b>              | 8536908085 |
| <b>Weight (Metric)</b>             | 0.136      |
| <b>Weight (Imperial)</b>           | 0.3        |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CCP-SAA](#)