

Specification Sheet

Part Number: FFE-2SSP



UV stable enclosure with IP55 (NEMA 4) sealing rating for long-term outdoor performance.

Detachable lid prevents access and can also be snapped back to allow unrestricted access inside.

Separation of inbound fiber from connectorized drop cables keeps fragile areas protected.

Pole or building/façade mounted to provide connections where they are needed.

Fiber Façade Enclosure, 7–10 mm, SC-PC Simplex, With Adapters And Pigtails Installed, Black, 1/pkg

Article Number	904-01321
Type	FFE-2SSP-PC-BK
Color	Black (BK)
Quantity Per	EA

<b>Product Description</b>	<p>The Fiber Façade Enclosure (FFE) features three separate areas to manage inbound cable, fiber splices and drop cables (customer connection). The inbound cable area has a dedicated entry port, supporting both cable end and mid-span applications with loop storage capacity for up to 1.5 m of excess fiber. The fiber splice area has capacity for a maximum of 24x heat shrink splices and maintains positive fiber management (30 mm minimum bend radius) throughout. The tray has a crossover facility that allows for alternative routing requirements and a fiber storage capacity of 1.5 m for 250µm fiber and 1.0 m of 900µm fiber. A PLC splitter (60 mm x 7 mm x 4 mm) can be fitted on the inside of the management area. The adapters are angled and spaced to allow for inspection prior to connection. Eight included anchor guides secure the drop cables (maximum diameter 6.0 mm). •8x SC/LC Simplex or LC Duplex customer connections. •Two inbound/pass-thru and 8 Outbound SC or LC Adapter ports support smaller MDU or SFU installations.</p>
<b>Short Description</b>	Fiber Façade Enclosure, 7–10 mm, SC-PC Simplex, With Adapters And Pigtails Installed, Black, 1/pkg
<b>Global Part Name</b>	FFE-2SSP-PC-BK-PC-BK
<b>Contents of pkg/kit</b>	FFE Enclosure (Black), Cable Entry Seal 7–10 mm, Splice Management Tray, 6x Tray Mounting Screws, OSP Cable Mounting Yoke with Screws, 2x 6-Position Heat Shrink Splice Bridge, 8x 3" Cable Ties, Wall Mounting Kit (4x Screws, Wall Anchors), Pole Mounting Kit (2x 30" UV Stable Cable Ties), 8x SC Simplex Adapters, 8x SC 900um 1m Pigtails, Installation Instructions
<b>Port Count</b>	8
<b>Length L (Imperial)</b>	9.5
<b>Length L (Metric)</b>	241.0
<b>Variant</b>	Outdoor Enclosure
<b>Width W (Imperial)</b>	6.1

<b>Width W (Metric)</b>	154.0
-------------------------	-------

<b>Height H (Imperial)</b>	2.84
----------------------------	------

<b>Height H (Metric)</b>	72.0
--------------------------	------

<b>Depth D (Imperial)</b>	2.84
---------------------------	------

<b>Depth D (Metric)</b>	72.0
-------------------------	------

<b>Material</b>	Polycarbonate (PC)
-----------------	--------------------

<b>Material Shortcut</b>	PC
--------------------------	----

<b>Package Quantity (Imperial)</b>	1
------------------------------------	---

<b>Package Quantity (Metric)</b>	1
----------------------------------	---

<b>Customs Number</b>	8536700000
-----------------------	------------

<b>Weight (Metric)</b>	0.606
------------------------	-------

<b>Weight (Imperial)</b>	1.34
--------------------------	------



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[FFE-2SSP](#)