

Specification Sheet

Part Number: CCP-L3A



Fully water sealed, achieving an IP-68 (NEMA 6P) rating, for use in wall or handhole installations.

Separate inbound/outbound access points ensure cable sealing and segregation.

Single subscriber splice or patch to connect a home or outdoor device.

Customer Connection Point, with LC Duplex Aqua Adapter, PC, Black, 1/pkg

Article Number	904-02024
Type	CCP-L3A
Color	Black (BK)
Quantity Per	EA
Product Description	<p>The Customer Connection Point (CCP) is manufactured from UL 94 V-0 and UV stable black polycarbonate and has a fully detachable snap-on lid. The closure has 2 separate cable access points which are sealed with a silicon cable entry kit (cable diameter range 4.6 mm - 5.6 mm) to maintain the IP68 rating. A GORE-TEX breather membrane is fitted to the lid to prevent condensation forming in the base of the closure. The unit can be supplied with one SC Simplex or LC Duplex and matching pigtails and provides splice management for two heat shrink splices. Internal fiber management features ensure that a 30 mm minimum bend radius is maintained within the closure and provides fiber storage capacity for any excess fiber.</p>

Short Description	Customer Connection Point, with LC Duplex Aqua Adapter, PC, Black, 1/pkg
Global Part Name	CCP-L3A-PC-BK
Width W (Imperial)	3.5
Width W (Metric)	89.0
Height H (Imperial)	6.30
Height H (Metric)	160.0
Material	Polycarbonate (PC)
Material Shortcut	PC
Package Quantity (Imperial)	1
Package Quantity (Metric)	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[CCP-L3A](#)