

## Technical data sheet

**Article number:**  
**156-02449**

**T50RIAHC2TSET**

<b>Product Group</b>	2-Piece Fixing Ties with Automatic Harness Clip, connectable and twistable 360°
<b>Product Family</b>	IAHC-Series
<b>Material</b>	Polyamide 6.6, heat stabilised (PA66HS), Polyamide 6.6, high impact modified, heat stabilised (PA66HIRHS)
<b>Colour</b>	Black (BK)
<b>Application Tool</b>	ProCut 9 no battery, MK3PNSP2, MK3SP, MK7HT, MK7P, MK20, MK21, EVO7SP, EVO7i, EVO7iSP, EVO9, EVO9i
<b>Bundle Diameter max (metric)</b>	20.0 mm
<b>Bundle Ø min.</b>	11.0 mm
<b>CE Certification</b>	No
<b>Fixation Method</b>	Omega Clip
<b>Flammability</b>	UL 94 HB
<b>Height (H)</b>	37.0 mm
<b>Length (L)</b>	202.0 mm
<b>Operating Temperature</b>	-40 °C to +105 °C
<b>Package Content packed in</b>	bag
<b>Pack Cont.</b>	1000 Bag
<b>ROHS compliant</b>	Yes
<b>Variant</b>	Inside Serrated
<b>Width (W)</b>	12 mm

**RoHS** 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[156-02449](#)