

611/621

611/621-Series

SMALL-SIZED ROCKER SWITCHES

The 611/621-Series small-size, sleek styling, actuator and termination choices make this switch a cost effective solution to most any switching need. International approvals, single or double pole circuitry, and ratings to 11A 125VAC further the broad appeal of this product family.



Product Highlights:

- Single or double pole
- Paddle and single color or dual color visi-rocker options
- UL, CSA and VDE approvals for select circuits
- Choice of 7 termination options

Typical Applications:

- Appliance
- Audio-Visual
- Power Supplies



Carling Technologies®
Innovative Designs. Powerful Solutions.

Carling Technologies, Inc.
60 Johnson Avenue, Plainville, CT 06062
Email: sales@carlingtech.com
Application Support: team2@carlingtech.com
Phone: 860.793.9281 Fax: 860.793.9231

www.carlingtech.com

Authorized Sales Representatives and Distributors

Click on a region of the map below to find your local representatives and distributors or visit www.carlingtech.com/findarep.



About Carling

Founded in 1920, Carling Technologies is a leading manufacturer of electrical and electronic switches and assemblies, circuit breakers, electronic controls, power distribution units, and multiplexed power distribution systems. With four ISO9001 and IATF16949 registered manufacturing facilities and technical sales offices worldwide, Carling Technologies Sales, Service and Engineering teams do much more than manufacture electrical components, they engineer powerful solutions! To learn more about Carling please visit www.carlingtech.com/company-profile.

To view all of Carling's environmental, quality, health & safety certifications please visit www.carlingtech.com/environmental-certifications

Worldwide Headquarters

Carling Technologies, Inc.
60 Johnson Avenue, Plainville, CT 06062
Phone: 860.793.9281 **Fax:** 860.793.9231
Email: sales@carlingtech.com

Northern Region Sales Office: nrsm@carlingtech.com
Southeast Region Sales Office: sersm@carlingtech.com
Midwest Region Sales Office: mrsm@carlingtech.com
West Region Sales Office: wrsm@carlingtech.com
Latin America Sales Office: larsm@carlingtech.com

Asia-Pacific Headquarters

Carling Technologies, Asia-Pacific Ltd.,
Suite 1607, 16/F Tower 2, The Gateway,
Harbour City, 25 Canton Road,
Tsimshatsui, Kowloon, Hong Kong
Phone: Int + 852-2737-2277 **Fax:** Int + 852-2736-9332
Email: sales@carlingtech.com.hk

Shenzhen, China: shenzhen@carlingtech.com
Shanghai, China: shanghai@carlingtech.com
Pune, India: india@carlingtech.com
Kaohsiung, Taiwan: taiwan@carlingtech.com
Yokohama, Japan: japan@carlingtech.com

Europe | Middle East | Africa Headquarters

Carling Technologies LTD
4 Airport Business Park, Exeter Airport,
Clyst Honiton, Exeter, Devon, EX5 2UL, UK
Phone: Int + 44 1392.364422 **Fax:** Int + 44 1392.364477
Email: ltd.sales@carlingtech.com

Germany: gmbh@carlingtech.com
France: sas@carlingtech.com



Carling Technologies®

Innovative Designs. Powerful Solutions.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Carling Technologies:

[62111461-0-0-N](#) [62111421-0-0-N](#) [62111481-0-0-N](#) [62112421-0-0-N](#) [62112422-0-0-N](#) [62112472-0-0-N](#) [62112926-0-0-N](#) [62115919-0-0-N](#) [62115919-0-9-V](#) [62115919-0-9-W](#) [62115919-E-0-V](#) [62115929-0-0-V](#) [62116919-0-0-N](#) [62116919-0-0-V](#) [62116919-0-9-V](#) [62116919-0-9-V-XN](#) [62115419-0-9-V](#) [62115919-0-8-V](#) [62112481-0-0-N](#) [62112431-0-0-N](#) [61111418-0-0-N](#) [62111471-0-0-N](#) [62111422-0-0-N](#) [62111119-0-0-N](#) [62111431-0-0-N](#) [62112482-0-0-N](#) [62111121-0-9-V](#) [62111429-0-0-N](#) [62111432-0-0-N](#) [62111482-0-0-N](#) [62111916-0-0-V](#) [62112221-0-0-N](#) [62112422-0-0-V](#) [62112918-0-9-V](#) [62115431-0-0-N](#) [62115929-0-8-V](#) [62115929-0-9-V](#) [62116919-0-8-V](#) [62116919-0-9-W](#) [62112461-0-0-N](#) [62112422-0-9-V](#) [61111471-0-0-N](#) [61112122-0-0-N](#) [61112461-0-0-N](#) [61111472-0-0-N](#) [62112461-0-0-V](#) [61112481-0-0-N](#) [61116929-0-0-N](#) [62112917-0-0-N](#) [62115929-0-A-N](#) [61115919-0-0-N](#) [61112472-0-0-N](#) [62112926-0-E-N](#) [62112481-0-9-V](#) [62116919-0-A-V](#) [62116929-0-E-N](#) [62116919-0-0-W](#) [62115929-0-E-N](#) [62116929-0-9-V](#) [61111461-0-0-N](#) [62111472-0-0-N](#) [61115929-0-0-N](#) [61112462-0-0-N](#) [62115919-E-0-N](#) [62111916-0-E-N](#) [62116929-0-0-N](#) [62112462-0-E-N](#) [61111462-0-0-N](#) [62116919-0-E-N](#) [62111461-0-0-V](#) [62112926-0-9-V](#) [62116929-0-0-V](#) [62112462-0-0-N](#) [62115929-0-0-N](#) [62112917-0-9-V](#) [62116929-0-A-W](#) [62112462-0-9-V](#) [62111462-0-0-N](#) [62111916-0-0-N](#) [62116919-0-A-W](#) [62111916-0-9-V](#) [61112471-0-0-N](#) [62112121-0-0-N](#) [61116919-0-0-N](#) [61112482-0-0-N](#) [62116929-0-9-W](#) [61112432-0-0-N](#) [62116929-0-8-V](#) [62112471-0-9-V](#) [62111481-0-0-V](#) [62112471-0-0-N](#) [62112431-0-0-V](#) [62115929-0-0-W](#) [62115919-0-E-N](#)