



Carling Technologies®
/// NOW PART OF



Littelfuse®

651/652-Series

Small-Sized Rocker Switches

PRODUCT WEBPAGE

request sample, configure part



This switch is ideal for applications with back panel size constraints. It fits in a standard rectangular cutout and is designed to provide ease of insertion along with superior panel retention qualities. A high profile rocker and butt-action contacts provide the user with a crisp positive-type feel. A variety of ratings, circuitry and termination choices will appeal to many market segments.

1
Pole

6-12
Amps

125-250
VAC

6-24
VDC

Typical Applications

- Handheld Appliances
- Audio-Visual
- Power Supplies

Authorized Sales Representatives and Distributors

Click on a region of the map below to find your local representatives and distributors or visit www.carlingtech.com/findarep.



About Carling

Founded in 1920, Carling Technologies is a leading manufacturer of electrical and electronic switches and assemblies, circuit breakers, electronic controls, power distribution units, and multiplexed power distribution systems. With six ISO9001 and IATF16949 registered manufacturing facilities and technical sales offices worldwide, Carling Technologies Sales, Service and Engineering teams do much more than manufacture electrical components, they engineer powerful solutions! To learn more about Carling please visit www.carlingtech.com/company-profile.

To view all of Carling's environmental, quality, health & safety certifications please visit www.carlingtech.com/environmental-certifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Carling Technologies:

[651121-BB-EN](#) [651122-BB-0N](#) [651122-WW-0N](#) [651262-BB-0N](#) [651882-BB-0N](#) [651122-BB-1V](#) [651262-BB-EN](#)
[651121-BB-0N](#) [651123-BB-0N](#) [651122-BB-1W](#) [651562-BB-0N](#) [651422-BB-0N](#) [651161-BB-0N](#) [652122-BB-AN](#)
[651163-BB-0N](#) [651111-BB-0N](#) [651122-BB-DN](#) [651112-BB-AN](#) [652121-BB-EN](#) [652412-WW-AN](#) [652124-BB-0N](#)
[651124-BB-0N](#) [651122-BB-AN](#) [651162-BB-EN](#) [652162-WW-0N](#) [651112-BB-0N](#) [652422-BB-0N](#) [651261-BB-0N](#)
[651122-BB-EN](#) [651162-BB-9V](#) [651192-BB-0N](#) [651172-BB-0N](#) [651162-BB-0N](#) [651122-BB-8V](#) [652121-BB-0N](#)
[651161-BB-EN](#) [651362-BB-0N](#) [651115-BB-EN](#) [651292-BB-0N](#) [652-122BB0N](#)