

| EXTENSION TUBES FOR VERTICAL FLOAT SWITCHES



A range of extension tubes available in Polypropylene or Stainless Steel (316L grade), which extend the reach of the various vertical float switches.

The Polypropylene tubes, with either M12 or M16 threads, are intended for use with our plastic types of float switches and are available in 250mm, 500mm and 750mm lengths.

Stainless steel extension tubes, with either 1/8BSP (G1/8), 3/8BSP (G3/8) or M16 threads, are intended for use with our stainless steel float switches and are available in lengths from 250mm to 1000mm.

Features

- Extends the reach of vertical switches
- Polypropylene extensions with M12 or M16 thread
- SS 316L extensions with G1/8, G3/8 or M16 thread


STANDARD PARTS

| Cynergy3 Part Material | Thread | Extension length | Gasket |
|---------------------------|----------|------------------|---------|
| EXT025M12PP Polypropylene | M12x1.75 | 250mm | Nitrile |
| EXT050M12PP Polypropylene | M12x1.75 | 500mm | Nitrile |
| EXT075M12PP Polypropylene | M12x1.75 | 750mm | Nitrile |
| EXT025M16PP Polypropylene | M16x2 | 250mm | Nitrile |
| EXT050M16PP Polypropylene | M16x2 | 500mm | Nitrile |
| EXT075M16PP Polypropylene | M16x2 | 750mm | Nitrile |
| EXT025G18SS SS 316L | G1/8 | 250mm | Nitrile |
| EXT050G18SS SS 316L | G1/8 | 500mm | Nitrile |
| EXT075G18SS SS 316L | G1/8 | 750mm | Nitrile |
| EXT100G18SS SS316L | G1/8 | 1000mm | Nitrile |
| EXT025G38SS SS 316L | G3/8 | 250mm | Nitrile |
| EXT050G38SS SS 316L | G3/8 | 500mm | Nitrile |
| EXT075G38SS SS 316L | G3/8 | 750mm | Nitrile |
| EXT100G38SS SS316L | G3/8 | 1000mm | Nitrile |
| EXT025M16SS SS316L | M16x2 | 250mm | Nitrile |
| EXT050M16SS SS 316L | M16x2 | 500mm | Nitrile |


Custom versions can be made for particular applications. Please contact Sensata with your requirements.



Polypropylene versions



Stainless steel SS 316L versions



Datasheets provided by Sensata Technologies, Inc., its subsidiaries and/or affiliates ("Sensata") are solely intended to assist third parties ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, valuation, and judgment in designing Buyer's systems and products. Sensata datasheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular datasheet. Sensata may make corrections, enhancements, improvements, and other changes to its datasheets or components without notice. Buyers are authorized to use Sensata datasheets with the Sensata component(s) identified in each particular datasheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATASHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATASHEETS OR USE OF THE DATASHEETS, EXPRESS, IMPLIED, OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATASHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com. SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY, AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA

CONTACT US

+44 (0)1202 897969
support@sensata.com
Sensata | Cynergy3
7 Cobham Road,
Ferndown Industrial Estate,
Wimborne, Dorset,
BH21 7PE, United Kingdom

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sensata:](#)

[EXT025G18SS](#) [EXT075M16PP](#) [EXT100G18SS](#) [EXT100G38SS](#) [EXT050M12PP](#) [EXT050M16PP](#) [EXT050M16SS](#)
[EXT075G18SS](#) [EXT075G38SS](#) [EXT075M12PP](#) [EXT025G38SS](#) [EXT025M12PP](#) [EXT025M16PP](#) [EXT025M16SS](#)
[EXT050G18SS](#) [EXT050G38SS](#)