

D

C

B

A


D

C

B

A

ZONE	REV.	REVISION DESCRIPTION	ECN NO.	DATE



TWISTED PAIR	COLOR	PIN	WIRE GAGE
PAIR 1	YELLOW	A	AWG 24
	W/YELLOW	C	
PAIR 2	BLUE	B	
	W/BLUE	E	AWG 22
PAIR 4	RED	D	
	BLACK	F	-
-	N/C	G	

APPLICATION NOTES;
1. FOR USE WITH SINGLE ENDED OUTPUT ENCODERS (AB, ABZ), AND DIFFERENTIAL OUTPUT ENCODERS WITH NO INDEX (ABC).
2. CABLE SHIELD IS NOT CONNECTED AT CONNECTOR. SHIELD CONNECTION MAY BE REQUIRED AT CONTROLLER END FOR SAFETY AND NOISE IMMUNITY.

PART NO.	CABLE LENGTH +5%/-0
31186-1610	10 FT
31186-1620	20 FT
31186-1630	30 FT
31186-1650	50 FT

- NOTES (UNLESS OTHERWISE INDICATED)
- MAT'L: MS3106F16S-1S INLINE PLUG (OR EQUIV.), 37048-003 CABLE, BLACK POLYURETHANE OVERMOLD
 - OPERATING TEMP -40 TO +80°C
 - STANDARD BEI (SENSATA), PINOUT/WIRE COLOR

UNCONTROLLED COPY

FIRST ISSUE DATE: 04/04/19
DRAWN: DRC
APPROVED: MFB
DATE: 04/04/19

ECN:

DATE:

MATERIAL:

DO NOT SCALE DRAWING

SENSATA TECHNOLOGIES PROPRIETARY AND CONFIDENTIAL. NEITHER THIS PRINT NOR THE INFORMATION CONTAINED HEREON IS TO BE USED AGAINST THE INTERESTS OF SENSATA TECHNOLOGIES OR AGAINST THE INTERESTS OF ANY OF ITS AFFILIATED COMPANIES OR WHOLLY OWNED SUBSIDIARIES.

INTERPRET DIMENSIONING AND TOLERANCING PER ASME Y14.5-2009. UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES[MILLIMETERS] AND ARE INTENDED AS NOMINAL SEE PRODUCT SPECIFICATIONS FOR MORE DETAILS.

THIRD ANGLE PROJECTION

BEI SENSORS
1461 LAWRENCE DRIVE
THOUSAND OAKS, CA 93120

Sensata Technologies

TITLE
M16 CONNECTOR AND CABLE ASSEMBLY

SIZE
B

DWG NO.
09911-002

REV.
.

SCALE 1:1
SOLIDWORKS
SHEET 1 OF 1

4

3

2

1

DEVICE:

PROJECT:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sensata:

[31186-1630](#) [31186-1610](#) [31186-1650](#) [31186-1620](#)