

D

C

B

A



D

C

B

A

ZONE	REV.	REVISION DESCRIPTION	ECN NO.	DATE
	.	.	.	.



PIN NO.	COLOR
1	WHITE
3	GREEN
4	YELLOW
5	GRAY
6	PINK
8	RED
2	BROWN
7	BLUE
SHIELD	BARE

PART NO.	LENGTH
31320-K81M	1 METER
31320-K85M	5 METER
31320-K86M	6 METER
31320-K810M	10 METER

NOTES;  
1. CABLE: 8 CONDUCTORS, 24 AWG, OVERALL SHIELD W/DRAIN WIRE, YELLOW POLYURETHANE JACKET  
CONTACTS: GOLD PLATED COPPER ALLOY  
SHELL: NICKEL PLATED BRASS  
2. INTENDED FOR DIFFERENTIAL LINE DRIVER OUTPUT ENCODERS  
3. RoHS 1,2 AND 3 COMPLIANT

UNCONTROLLED COPY

FIRST ISSUE DATE: 06/25/19  
DRAWN: DRC  
APPROVED: MFB  
DATE: 06/25/19

ECN:  
  
DATE:  
  
MATERIAL:

SENSATA TECHNOLOGIES PROPRIETARY AND CONFIDENTIAL. NEITHER THIS PRINT NOR THE INFORMATION CONTAINED HEREON IS TO BE USED AGAINST THE INTERESTS OF SENSATA TECHNOLOGIES OR AGAINST THE INTERESTS OF ANY OF ITS AFFILIATED COMPANIES OR WHOLLY OWNED SUBSIDIARIES.

INTERPRET DIMENSIONING AND TOLERANCING PER ASME Y14.5-2009. UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES[MILLIMETERS] AND ARE INTENDED AS NOMINAL SEE PRODUCT SPECIFICATIONS FOR MORE DETAILS.

DO NOT SCALE DRAWING

THIRD ANGLE PROJECTION

BEI SENSORS  
1461 LAWRENCE DRIVE  
THOUSAND OAKS, CA 93120

TITLE  
**K8 CONNECTOR AND CABLE ASSEMBLY**

SIZE  
**B**

DWG NO.  
**09926-001**

REV.

SCALE 1:1 SOLIDWORKS SHEET 1 OF 1

4

3

2

DEVICE: PROJECT:

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sensata:

[31320-K85M](#) [31320-K810M](#) [31320-K86M](#) [31320-K81M](#)