

60x60x15mm

Model	P/N	Bearing ● Sleeve ● 2BALL	Rating Voltage (VDC)	Power Current (mA)	Power Consumption (WATTS)	Speed (RPM)	Air Flow (CFM)	Static Pressure (Inch-H ₂ O)	Noise (dBA)	Weight (g)
KD0506PHS2	GN	●	5	187	0.9	3800	18.0	0.14	31.0	44
KD0506PHS3	GN	●	5	115	0.6	3000	15.0	0.12	25.0	44
KD1206PHS1	GN	●	12	153	1.8	4300	21.0	0.18	36.0	42
KD1206PHS2	GN	●	12	93	1.1	3800	18.0	0.14	31.0	42
KD1206PHS3	GN	●	12	62	0.7	3000	15.0	0.12	25.0	42
KD2406PHS1	GN	●	24	86	2.1	4300	21.0	0.18	36.0	44
KD2406PHS2	GN	●	24	56	1.3	3800	18.0	0.14	31.0	44

60x60x20 mm

Model	P/N	Bearing	(VDC)	(mA)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KD1206PKB1	(2).GN	●	12	154	1.9	4500	23.0	0.18	34.5	52
KD1206PKB2	(2).GN	●	12	88	1.1	3700	19.0	0.14	29.0	52
KD1206PKS1	GN	●	12	154	1.9	4500	23.0	0.18	33.5	52
KD1206PKS2	GN	●	12	90	1.1	3700	19.0	0.14	28.0	52

60x60x25mm

Model	P/N	Bearing	(VDC)	(mA)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KD1206PTB1	(2).GN	●	12	148	1.8	4500	23.5	0.21	34.5	55
KD1206PTB2	(2).GN	●	12	87	1.0	3800	19.3	0.15	30.0	55
KD1206PTS1	GN	●	12	151	1.8	4500	23.5	0.21	33.5	55
KD1206PTS2	GN	●	12	89	1.1	3800	19.3	0.15	29.0	55


70x70x15mm

Model	P/N	Bearing	(VDC)	(mA)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KD0507PHB2	(2).GN	●	5	218	1.1	2800	23.0	0.09	27.5	52
KD0507PHB3	(2).GN	●	5	130	0.7	2300	19.0	0.07	22.5	52
KD0507PHS2	GN	●	5	218	1.1	2800	23.0	0.09	26.5	52
KD0507PHS3	GN	●	5	131	0.7	2300	19.0	0.07	21.5	52
KD1207PHB1	(2).GN	●	12	173	2.1	3300	27.0	0.11	32.5	50
KD1207PHB2	(2).GN	●	12	104	1.3	2800	23.0	0.09	27.5	50
KD1207PHB3	(2).GN	●	12	66	0.8	2300	19.0	0.07	22.5	50
KD1207PHS1	GN	●	12	171	2.1	3300	27.0	0.11	31.5	50
KD1207PHS2	GN	●	12	102	1.2	2800	23.0	0.09	26.5	50
KD1207PHS3	GN	●	12	67	0.8	2300	19.0	0.07	21.5	50

70x70x20 mm

Model	P/N	Bearing	(VDC)	(mA)	(WATTS)	(RPM)	(CFM)	(Inch-H ₂ O)	(dBA)	(g)
KD1207PKB1	13.(2).GN	●	12	130	1.6	3200	29.0	0.14	33.5	66
KD1207PKB2	13.(2).GN	●	12	100	1.2	2900	27.0	0.12	31.0	66
KD1207PKB3	13.(2).GN	●	12	80	1.0	2600	23.5	0.09	27.0	66
KD1207PKS1	13.GN	●	12	140	1.7	3200	29.0	0.14	33.0	66
KD1207PKS2	13.GN	●	12	110	1.3	2900	27.0	0.12	30.0	66
KD1207PKS3	13.GN	●	12	80	1.0	2600	23.5	0.09	26.0	66
KD2407PKB1	13.(2).A.GN	●	24	60	1.4	3200	29.0	0.14	33.5	68
KD2407PKB2	13.(2).A.GN	●	24	50	1.2	2900	27.0	0.12	31.0	68
KD2407PKB3	13.(2).A.GN	●	24	40	1.0	2600	23.5	0.09	27.0	68
KD2407PKS1	13.A.GN	●	24	60	1.4	3200	29.0	0.14	33.0	68
KD2407PKS2	13.A.GN	●	24	50	1.2	2900	27.0	0.12	30.0	68
KD2407PKS3	13.A.GN	●	24	40	1.0	2600	23.5	0.09	26.0	68

DC Brushless Fan Model Numbering System



P/N

Example: KD1205PHB1 P/N:(2).GN

- 11/13 Motor model
- (2) Two ball bearing
- G Big hub
- (9) 9 Blades
- GN RoHS compliance

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sunon:

[KD2406PHS2.GN](#) [KD2406PHS1.GN](#)